

Wearable Device for Assured Attention Silwatch

Certified Country: Thailand

The device quickly and surely informs only those whom you want to communicate with of the production line status with a "vibration" and "message".



- The transmitter has one push button and two external inputs. (Three types of messages can be sent with one transmitter.)
- The wristwatch receiver can display a message of up to 20 characters.
- Individual, group, and simultaneous calls can be used freely.
- Approximate communication distance is an unobstructed 170-200m, (186-219 yd) and 80-100m (87-109 yd) indoors. By installing or adding repeaters, you can communicate to more distant places and wide areas.
- A combination of multiple transmitters and wristwatch receivers can be used.

Silwatch Transmitter

SW-N124T

Silwatch Transmitter



Input
1 Push Button
2 External Inputs

SW-0123T

Silwatch Repeater



SWR-2130T

Wristwatch Receiver



- Notifying calls by vibration and message.
- Rechargeable (using the optional charger SWC-1140)
- Clock function
- Memory function
- Maximum of 20 characters for display


SWC-1140

Charger



Item	SW-N124T	SW-0123T	SWR-2130T	SWC-1140
Frequency in Use	426.05MHz			
Input(s)	1 Push Button 2 External Inputs (non-voltage contacts)	—	4 Buttons (MENU,UP,DOWN,SELECT)	—
Display	1 Green LED (lighting when transmitting)		LCD (max. 20 characters)	
Power Source	AC100-240V (using included AC adapter) or 2 AAA-Size Batteries		Rechargeable (lithium-ion battery 3.7V)	AC100-240V (using included AC adapter)
Power Consumption	50mA or Less	15mA or Less	150mA or Less	70mA or Less
Operating Environment	Temperature: -10 to 50° C (14-122° F)			
External Dimensions (W x H x D)	65 x 62 x 24 mm (2.6 x 2.4 x 0.9") (excluding protrusions)		43 x 38 x 16 mm (1.7 x 1.5 x 0.6") (excluding protrusions)	84 x 46 x 31 mm (3.3 x 1.8 x 1.2") (excluding protrusions)
Weight	Approx. 80 g (2.8 oz)	Approx. 80 g (2.8 oz)	Approx. 45 g (1.4 oz) (including battery and strap)	Approx. 60 g (2.1 oz)
Battery Life	2.5 Months (when transmitted once an hour)	1 Year (when transmitted once an hour)	4 Days (use 5-6 times a day)	—
Accessory	AC Adapter, Contact Input Cable	AC Adapter	—	AC Adapter
Remarks	—	—	A full charge in about 3 hours	


CASE1



CASE2



CASE3



CASE4

